

### **Features**

- **Various colors**
- **High energy efficiency**
- **Low voltage**
- **Suitable for all SMT assembly methods**
- **Long operating life**




### **Typical Applications**

- **Effect and accent lighting: display cases, front panels**
- **Architectural lighting: flood lights, stairway lighting, garden lighting**
- **Room lighting: contour lighting, chandeliers, pendants, coves**
- **Specialty lighting: security lighting, portable flashlight, reading lamps**

**Package Outlines**

**Lambertian**



**Notes:**

1. All dimensions are in mm.
2. Drawings are not to scale.
3. It is strongly recommended that the temperature of lead be not higher than  $55^{\circ}\text{C}$ .

### Absolute Maximum Ratings

Parameter	Symbol	Rating	Units
DC Forward Current	$I_F$	350	mA
Peak pulse current;(tp ≤ 100 s, Duty cycle=0.25)	$I_{pulse}$	500	mA
Reverse Voltage	$V_R$	5	V
Reverse Current( $V_R=5V$ )	$I_R$	50	$\mu A$
LED junction Temperature ( at 350 mA)	$T_j$	125	°C
Operating Temperature	$T_{opr}$	-30 ~ +110	°C
Storage Temperature	$T_{stg}$	-40 ~ +120	°C
Manual Soldering Time at 260°C(Max.)	$T_{sol}$	5	seconds

### Luminous Flux Characteristics at $I_F=350mA$ ( $T_a=25^\circ C$ , $T_{opr}=100ms$ ):

Lens Item	Part Name	Color	Flux			Units
			Min.	Typ.	Max.	
Lambertian	VAOL-SW1xAx-SA	White	70.3	90.0	--	lm
	VAOL-SX1xAx-SA	Warm White	63.0	80.0	--	lm
	VAOL-SR1xAx-SA	Red	30.0	50.0	--	lm
	VAOL-SO1xAx-SA	Red Orange	33.3	55.0	--	lm
	VAOL-SA1xAx-SA	Amber	30.0	50.0	--	lm
	VAOL-ST1xAx-SA	True Green	70.3	90.0	--	lm
	VAOL-SB1xAx-SA	Blue	20.3	35.0	--	lm

**Forward Voltage Characteristics at  $I_F=350\text{mA}$  ( $T_a=25^\circ\text{C}$ ,  $T_{opr}=100\text{ms}$ ):**

Lens Item	Part Name	Color	$V_F$			Units
			Min.	Typ.	Max.	
	VAOL-SW1xAx-SA	White	3.1	--	4.3	V
	VAOL-SX1xAx-SA	Warm White	3.1	--	4.3	V
	VAOL-SR1xAx-SA	Red	2.0	--	3.0	V
	VAOL-SO1xAx-SA	Red Orange	2.0	--	3.0	V
	VAOL-SA1xAx-SA	Amber	2.0	--	3.0	V
	VAOL-ST1xAx-SA	True Green	2.8	--	4.0	V
	VAOL-SB1xAx-SA	Blue	3.1	--	4.3	V

**Wavelength or Color Temperature Characteristics at  $I_F=350\text{mA}$  ( $T_a=25^\circ\text{C}$ ,  $T_{opr}=100\text{ms}$ ):**

Lens Item	Part Name	Color	$\lambda_d/\text{CCT}$			Units
			Min.	Typ.	Max.	
	VAOL-SW1xAx-SA	White	5000	--	8000	K
	VAOL-SX1xAx-SA	Warm White	2800	--	3800	K
	VAOL-SR1xAx-SA	Red	620	--	630	nm
	VAOL-SO1xAx-SA	Red Orange	610	--	620	nm
	VAOL-SA1xAx-SA	Amber	585	--	595	nm
	VAOL-ST1xAx-SA	True Green	515	--	535	nm
	VAOL-SB1xAx-SA	Blue	460	--	475	nm

**Temperature Coefficient of Forward Voltage & Thermal Resistance Junction to Board Characteristics at  $I_F=350\text{mA}$  ( $T_a=25^\circ\text{C}$ ):**


Lens Item	Part Name	Color	$\Delta V_F/\Delta T$		$R_{\theta J-B}$	
			Typ.	Units	Typ.	Units
	VAOL-SW1xAx-SA	White	-2	$\text{mV}/^\circ\text{C}$	20	$^\circ\text{C}/\text{W}$
	VAOL-SX1xAx-SA	Warm White	-2	$\text{mV}/^\circ\text{C}$	20	$^\circ\text{C}/\text{W}$
	VAOL-SR1xAx-SA	Red	-2	$\text{mV}/^\circ\text{C}$	20	$^\circ\text{C}/\text{W}$
	VAOL-SO1xAx-SA	Red Orange	-2	$\text{mV}/^\circ\text{C}$	20	$^\circ\text{C}/\text{W}$
	VAOL-SA1xAx-SA	Amber	-2	$\text{mV}/^\circ\text{C}$	20	$^\circ\text{C}/\text{W}$
	VAOL-ST1xAx-SA	True Green	-2	$\text{mV}/^\circ\text{C}$	20	$^\circ\text{C}/\text{W}$
	VAOL-SB1xAx-SA	Blue	-2	$\text{mV}/^\circ\text{C}$	20	$^\circ\text{C}/\text{W}$

**Emission Angle Characteristics at  $I_F=350\text{mA}(T_a=25^\circ\text{C})$ :**

Part Name	Color	$2\theta$ (Typ.)	Units
VAOL-SW1xAx-SA	White	130	Degrees
VAOL-SX1xAx-SA	Warm White	130	Degrees
VAOL-SR1xAx-SA	Red	120	Degrees
VAOL-SO1xAx-SA	Red Orange	120	Degrees
VAOL-SA1xAx-SA	Amber	120	Degrees
VAOL-ST1xAx-SA	True Green	150	Degrees
VAOL-SB1xAx-SA	Blue	150	Degrees

**Typical Radiation Pattern for**

**Lambertian**






Specific binning requirements- please contact our home office



**Note**

1. Flux is measured with an accuracy of  $\pm 10\%$ .
2. CCT selection acc. to CCT groups and an accuracy of  $\pm 200\text{K}$
3. Forward Voltage is measured with an accuracy of  $\pm 0.1\text{V}$
4. Wavelength is measured with an accuracy of  $\pm 0.5\text{nm}$
5. All white 、 warm white 、 True green and blue emitters are built with InGaN
6. All red 、 red-orange and amber emitters are built with AlGaInP


### Electrical & Optical Curves-Spectrum




### Typical Optical and Electrical Curves




### Typical Optical and Electrical Curves




Operating Current & Ambient Temperature



Forward Current & Luminous Flux



Forward Current & Wavelength



**Package Specifications**

